

Product data sheet

Specifications



Thorsman Glands - cable gland - grey - M16 - diameter 4 to 8

ISM71502

Main

Product Range	Thorsman Glands
Product Type	Cable gland
Colour	Grey (RAL 7035)
Quantity Per Package	Set of 20

Complementary

Material	PA6
Iso Thread	M16
Cable Outer Diameter	4...8 mm

Environment

Ip-Class	IP68
Operating Temperature	-30...80 °C permanently -30...150 °C intermittently

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	15 cm
Package 1 Length	20 cm
Package 1 Weight	8 g
Unit Type Of Package 2	BAG
Number Of Units In Package 2	20
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	6 cm
Package 2 Weight	222 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	1500
Package 3 Height	30 cm
Package 3 Width	38 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 3 Length	56 cm
Package 3 Weight	17.2 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Toxic Heavy Metal Free

 Mercury Free

 Rohs Exemption Information [Yes](#)

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
--------------------------	---

China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
------------------------------	---