



Main

Product range	Thorsman Glands
Product type	Cable gland
Colour	Grey (RAL 7035)
Quantity per package	Set of 10

Complementary

Material	PA6
ISO thread	M25
Cable outer diameter	11...17 mm

Environment

IP-Class	IP68
Operating temperature	-30...80 °C permanently -30...150 °C intermittently

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	21 g
Package 1 Height	4 cm
Package 1 width	19 cm
Package 1 Length	19 cm
Unit Type of Package 2	BAG
Number of Units in Package 2	10
Package 2 Weight	2.11 kg
Package 2 Height	10 cm
Package 2 width	10 cm
Package 2 Length	4 cm
Package 3 Height	25 cm

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------