

# Product data sheet

Specifications



## cam switch operating head - with metallic legend - 60 ° switching angle

KBA1ZR1

 **Discontinued on:** Jan 29, 2021

 **Discontinued**

### Main

Range Of Product	Harmony Series K
Product Or Component Type	Cam switch operating head
Component Name	KBA
Product Compatibility	Front mounting bodies 12 and 20 A by Ø 22 mm hole
Cam Switch Head Type	With bezel Ø 29 mm, plastic with metallic finish
Type Of Operator	key Ronis 8R15
Rotary Handle Padlocking	Without
Presentation Of Legend	With metallic legend
Switching Angle	60 °

### Complementary

Mechanical Durability	1000000 cycles
Cad Overall Width	29 mm
Cad Overall Height	29 mm
Cad Overall Depth	69 mm
Net Weight	0.057 kg
Compatibility Code	KBA

### Environment

Protective Treatment	TC
Ambient Air Temperature For Operation	-25...55 °C
Ambient Air Temperature For Storage	-40...70 °C
Shock Resistance	30 gn conforming to IEC 68-2-27
Vibration Resistance	5 gn conforming to IEC 68-2-6 (f = 10...150 Hz)
Ip Degree Of Protection	IP65 conforming to IEC 529 IP65 conforming to NF C 20-010

### Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications