

Product data sheet

Specifications



Li-ion Battery Rack Type E - IEC

LIBATTSMGEIEC

Overview

Presentation	Battery cabinet that includes Lithium-Ion batteries, Battery Management System (BMS), switchgear, power supply, and communication interface. Compatible with the Galaxy VS UPS.
Lead Time	Usually Ships within 2 Weeks

Main

Battery Type	Li-Ion (Lithium-Ion)
Provided Equipment	User manual

Batteries & Runtime

Battery Location	Battery cabinet
Number Of Battery Free Slots	0
Number Of Battery Filled Slots	0
Battery Manufacturer	Samsung
Device Mounting	Enclosed battery cabinet
Battery Voltage	516.8 V
Battery Power In Vah	67 VAh

Physical

Colour	White
Height	205.5 cm
Width	65 cm
Depth	59.9 cm
Net Weight	533 kg
Mounting Mode	Not rack-mountable

Output

Battery Capacity	67000 mA.h
------------------	------------

Conformance

Product Certifications	CE
------------------------	----

Environmental

Ambient Air Temperature For Operation	18...28 °C
---------------------------------------	------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Storage	0...40 °C
Storage Relative Humidity	0...60 %

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	220 cm
Package 1 Width	60 cm
Package 1 Length	120 cm
Package 1 Weight	553 kg

Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Not applicable, out of EU RoHS legal scope
