

Product data sheet

Specifications



Li-Ion Battery 9540A - Battery Rack UL 17 modules Type G for GVX, GVM, G7K

LIBSMG95GUL

! Discontinued

! Discontinued on: Jan 6, 2022

! End-of-service on: Oct 18, 2023

Overview

Presentation	UL 9540A tested Li-Ion Battery Cabinet with 17 battery modules (Type G) for GVX, GVM, G7K UPS (UL standard)
Lead Time	Usually Ships within 2 Weeks

Main

Product Or Component Type	Battery cabinet
Battery Type	Li-Ion (Lithium-Ion)
Provided Equipment	User manual

Batteries & Runtime

Battery Location	Battery cabinet
Number Of Battery Free Slots	0
Number Of Battery Filled Slots	0
Battery Manufacturer	Samsung
Device Mounting	Enclosed battery cabinet
Battery Voltage	516.8 V

Physical

Colour	White
Height	205.5 cm
Width	65 cm
Depth	53 cm
Net Weight	510 kg
Mounting Mode	Not rack-mountable

Output

Battery Capacity	67000 mA.h
------------------	------------

Conformance

Standards	IBC 2015
Product Certifications	UL listed

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental

Ambient Air Temperature For Operation	18...28 °C
Ambient Air Temperature For Storage	0...40 °C
Storage Relative Humidity	0...60 %

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	220 cm
Package 1 Width	53 cm
Package 1 Length	120 cm
Package 1 Weight	530 kg

Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------