

Product data sheet

Specifications



Easy Styl, cover frame, 2 modules, silver

LMR7262004

Main

Range	Easy Styl
Product Or Component Type	Cover frame
Device Presentation	Basic element
Colour Tint	Silver

Complementary

Range Compatibility	Easy Styl
Number Of Modules	2 modules
Height	81 mm
Depth	9.5 mm
Width	87 mm
Fixing Mode	Clip-in
Net Weight	0.017 kg

Environment

Ip Degree Of Protection	IP20
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.500 cm
Package 1 Width	8.000 cm
Package 1 Length	9.000 cm
Package 1 Weight	18.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	20
Package 2 Height	8.500 cm
Package 2 Width	14.500 cm
Package 2 Length	26.500 cm
Package 2 Weight	415.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	200

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	4.448 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation