


Product data sheet

Specifications



Current transformer, FuPacT ISFL250 to ISFL1250, class 1, 400/5A, 5VA

LV480887

Main

Range Of Product	ISFL1250 ISFL250...630
Range	FuPacT
Product Or Component Type	Current transformer
Device Application	Power supply
Range Compatibility	FuPacT FuPacT ISFL ISFL250 fuse-switch disconnecter FuPacT FuPacT ISFL ISFL400 FuPacT FuPacT ISFL ISFL630 FuPacT FuPacT ISFL ISFL1250
Current Transformer Ratio	400/5 A
Power Consumption In Va	5 VA

Complementary

Accessory / Separate Part Category	Measurement accessory
Current Transformer Type	Measurement class 1
Maximum Safety Factor	5
[Ue] Rated Operational Voltage	800 V AC 50/60 Hz
Ip Degree Of Protection	IP20
Standards	IEC 60044-1 VDE 0414 BS 7626
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...80 °C
Height	78 mm
Width	60 mm
Depth	30 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.6 cm
Package 1 Width	6.5 cm
Package 1 Length	8.0 cm
Package 1 Weight	163.0 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	S02
Number Of Units In Package 2	40
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	6.975 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations