

Product data sheet

Specifications



Unica - Complete TV/FM socket - terminal socket - ivory/ivory

MGU10.452.25D

 **Discontinued on:** Apr 28, 2014

 **Discontinued**

Main

Range	Unica
Aesthetic Name	Unica (standard aesthetic)
Product Or Component Type	TV/FM socket
Device Presentation	Complete product
Tv Socket Type	End-of-line (terminal socket)
Colour Tint	Ivory
Condition Of Use	Series distribution systems

Complementary

Tv Connector	Male IEC 9.52 mm
Radio Connector	Female IEC 9.52 mm
Path Attenuation	13.5 dB TV/UHF signal125...860 MHz 13.5 dB TV/VHF signal47...68 MHz 27 dB R signal87.5...108 MHz
Dc Current Flow	Yes
Number Per Line	1
Number Of Modules	2 modules
Material	ABS (acrylonitrile butadiene-styrene): cover frame ASA + PC: mechanism cover PBT (polybutylene terephthalate) GF30: fixing frame
Fixing Mode	Short claws
Depth	28 mm
Width	85 mm
Height	80 mm
Embedding Depth	18 mm
Net Weight	0.106 kg

Environment

Ip Degree Of Protection	IP20
Ik Degree Of Protection	IK01
Ambient Air Temperature For Operation	15...35 °C
Ambient Air Temperature For Storage	0...35 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental Characteristic	Oil
	Alcohol
	UV resistant
	Window-cleaning fluid
	Petrol
	Bleach
	Liquid soap
	Acetone
Standards	EN 50083-2
	EMC directive
	EN 50083-4
	EN 50083-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	8 cm
Package 1 Length	8.5 cm
Package 1 Weight	90 g

Contractual warranty

Warranty	18 months
----------	-----------