

Product data sheet

Specifications



Unica - complete rotary dimmer - 230 VAC - 40...400 W/VA - ivory/cream

MGU10.511.559D

⚠ Discontinued on: Dec 31, 2015

⚠ Discontinued

Main

Aesthetic Name	Unica (standard aesthetic)
Aesthetic Cover Frame Name	Unica Basic
Product Or Component Type	Dimmer
Device Presentation	Complete product
Fixing Mode	Short claws
[Ue] Rated Operational Voltage	230 V AC 50 Hz
Number Of Modules	2 modules
Colour Tint	Insert: ivory Cover frame: cream

Complementary

Dimmer Control	Rotary push type
Maximum Permanent Current	1.74 A
Total Number Of Wires	2
Load Type	230 V AC halogen lamp - 40...400 W 230 V AC incandescent lamp - 40...400 W Low voltage halogen lamp with ferromagnetic transformer - 40...400 VA Low voltage halogen lamp with electronic transformer - 40...400 VA
Protection Type	Fuse protection
Fuse Type	4 Ah 5 x 20 mm 230 V 50 Hz
Marking	L+N
Connections - Terminals	Screw terminals
Clamping Connection Capacity	<= 2 x 2.5 mm ² for flexible cable(s) <= 2 x 2.5 mm ² for rigid cable(s)
Connected Auxiliaries	2-way switch
Material	ABS (acrylonitrile butadiene-styrene): cover frame ASA + PC: mechanism cover PBT (polybutylene terephthalate) GF30: fixing frame
Standards	EN 60669-2-1
Product Certifications	CE
Ambient Air Temperature For Operation	5...30 °C
Ambient Air Temperature For Storage	-20...60 °C
Embedding Depth	34 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Depth	54 mm
Width	85 mm
Height	80 mm
Net Weight	0.1045 kg

Environment

Ik Degree Of Protection	IK01
Ip Degree Of Protection	IP20
Environmental Characteristic	Window-cleaning fluid Petrol Alcohol UV resistant Liquid soap Oil Bleach Acetone

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	1 kg

Contractual warranty

Warranty	18 months
----------	-----------