


# Product data sheet

Specifications



## Unica - 1 S.O. - 2P+E, US - 1 m - ivory

MGU3.027.25

 **Discontinued on:** May 30, 2014

 **Discontinued**

### Main

|                             |                            |
|-----------------------------|----------------------------|
| Range                       | Unica                      |
| Product Or Component Type   | Socket-outlet              |
| Aesthetic Name              | Unica (standard aesthetic) |
| Device Presentation         | Mechanism                  |
| Device Mounting             | Flush                      |
| Socket Number               | 1                          |
| Outlet Poles Configuration  | 2P + E                     |
| Outlet Standard             | American                   |
| Outlet Standard Description | Displaced earth            |
| Rated Current               | 15 A                       |

### Complementary

|                                |   |
|--------------------------------|---|
| Device Application             | Power supply  |
| [Ue] Rated Operational Voltage | 127 V   |
| Network Type                   | AC  |
| Network Frequency              | 50/60 Hz  |
| Number Of Modules              | 1 module  |
| Fixing Mode                    | Clip-in   |
| Colour Tint                    | Cream (RAL 9010)  |
| Connections - Terminals        | Screw terminals   |
| Cable Cross Section            | 0...4 mm <sup>2</sup> - cable stiffness: flexible<br>0...4 mm <sup>2</sup> - cable stiffness: rigid |
| Minimum Load Breaking Capacity | 100 operations 1.25 In and 1.1 Un, cos phi = 0.6  |
| Electrical Durability          | 10000 cycles, cos phi = 0.8   |
| Insulation Resistance          | > 5 MOhm at 500 V   |
| Dielectric Strength            | 2000 V  |
| Material                       | ASA + PC: mechanism cover   |
| Surface Finish                 | Brilliant   |
| Quantity Per Set               | Set of 1 blister  |
| Embedding Depth                | 24 mm   |
| Depth                          | 33 mm   |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                   |           |
|-------------------|-----------|
| Width             | 22.5 mm   |
| Height            | 45 mm     |
| Net Weight        | 0.0235 kg |
| Surface Treatment | Untreated |

## Environment

|                                       |   |
|---------------------------------------|---|
| Ambient Air Temperature For Operation | 15...30 °C  |
| Ambient Air Temperature For Storage   | 0...35 °C   |
| Ik Degree Of Protection               | IK01  |
| Ip Degree Of Protection               | IP20  |
| Environmental Characteristic          | Bleach<br>Window-cleaning fluid<br>Liquid soap<br>Oil<br>Petrol<br>Alcohol<br>Acetone<br>UV resistant |

## Packing Units

|                              |        |
|------------------------------|--------|
| Unit Type Of Package 1       | PCE    |
| Number Of Units In Package 1 | 1      |
| Package 1 Height             | 6.7 cm |
| Package 1 Width              | 4.4 cm |
| Package 1 Length             | 6.8 cm |
| Package 1 Weight             | 24 g   |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|