

# Product data sheet

Specifications



## Unica - push-button - 1-way - 10 A 250 VAC - 1 m - ivory

MGU3.106T.25N

⚠ Discontinued on: Jun 15, 2023

⚠ Discontinued

### Main

Range Of Product	Unica
Aesthetic Name	Unica (standard aesthetic)
Product Or Component Type	Push-button
Device Presentation	Mechanism
Technology Type	Electromechanical
Switch Function	1-pole 1-way
Number Of Rocker	1
Device Application	Light control
Colour Tint	Ivory

### Complementary

Rated Current	10 A
[Ue] Rated Operational Voltage	250 V
Network Type	AC
Network Frequency	50/60 Hz
Electrical Durability	40000 cycles, cos phi = 0.6
Insulation Resistance	> 5 MOhm at 500 V
Dielectric Strength	2000 V
Minimum Load Breaking Capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Condition Of Use	Impulse relay control
Opening Distance	> 3 mm
Actuator	Push-button
Number Of Modules	1 module
Pilot Light	LED, colour: blue, current consumption: 0.15 mA, temperature rise: 15 °C
Connections - Terminals	Screw terminals
Cable Cross Section	0...2.5 mm² rigid cable 0...2.5 mm² flexible cable
Material	ASA + PC: mechanism cover
Fixing Mode	Clip-in
Width	22.5 mm
Height	45 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Depth	33 mm
Embedding Depth	21 mm
Net Weight	0.0209 kg
Ambient Air Temperature For Operation	25...35 °C
Ambient Air Temperature For Storage	0...50 °C
Standards	LV directive EN 60669-1 EMC directive

## Environment

Ip Degree Of Protection	IP20
Ik Degree Of Protection	IK01
Environmental Characteristic	Petrol Alcohol Bleach Oil UV resistant Acetone Liquid soap Window-cleaning fluid

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.7 cm
Package 1 Width	4.4 cm
Package 1 Length	6.8 cm
Package 1 Weight	18.5 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	33.5 cm
Package 2 Width	4.4 cm
Package 2 Length	13.6 cm
Package 2 Weight	185.0 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations