

Product data sheet

Specifications



Unica - rocker switch - 10 A, 250 VAC - 2 m - ivory

MGU3.208.25

 **Discontinued on:** Feb 21, 2024

 **Discontinued**

Main

Range	Unica
Device Application	Control
Product Or Component Type	Shutter control
Aesthetic Name	Unica (standard aesthetic)
Device Presentation	Mechanism
Rated Current	10 A
[Ue] Rated Operational Voltage	250 V
Network Type	AC
Network Frequency	50/60 Hz
Fixing Mode	Clip-in
Colour Tint	Ivory

Complementary

Device Mounting	Flush
Number Of Modules	2 modules
Technology Type	Electromechanical
Actuator	Rocker
Number Of Rocker	2
Switch Function	1-pole 2-way
Switch Application	Roller blind
Contacts Type And Composition	1 C/O
Mechanical Interlocking	Interlock between up/down
[Iu] Rated Interrupted Current	2.5 A for motor
Opening Distance	> 3 mm
Marking	UP Down
Connections - Terminals	Screwless terminals
Cable Cross Section	2.5 mm² flexible cable 2.5 mm² rigid cable
Minimum Load Breaking Capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Electrical Durability	40000 cycles, cos phi = 0.6

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Insulation Resistance	> 5 MOhm at 500 V
Dielectric Strength	2000 V
Material	ASA + PC: mechanism cover
Standards	EMC directive EN 60669-1 LV directive
Ambient Air Temperature For Operation	25...35 °C
Ambient Air Temperature For Storage	0...50 °C
Embedding Depth	22 mm
Depth	34 mm
Width	45 mm
Height	45 mm
Net Weight	0.0351 kg

Environment

Ik Degree Of Protection	IK01
Ip Degree Of Protection	IP20
Environmental Characteristic	Liquid soap Window-cleaning fluid UV resistant Alcohol Oil Acetone Bleach Petrol

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	6.500 cm
Package 1 Length	6.500 cm
Package 1 Weight	37.800 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	4.500 cm
Package 2 Width	13.500 cm
Package 2 Length	33.000 cm
Package 2 Weight	451.000 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	40
Package 3 Height	15.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	2.030 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations