

# Product data sheet

Specifications



## Unica - 1 RJ45 socket (S-One) - 1 m - Cat.6, UTP - white

MGU3.414.18

⚠ Discontinued on: Feb 29, 2024

⚠ Discontinued

### Main

Range	Unica
Aesthetic Name	Unica (standard aesthetic)
Product Or Component Type	Data socket
Device Presentation	Mechanism
Colour Tint	White (RAL 9003)
Data Socket Type	RJ45 8 contact(s) Cat.6 < 250 MHz
Provided Equipment	Label holder Protective flap

### Complementary

Communication Network Type	1000BASE-TX
Communication Port Protocol	ATM 1200 Mbps
Number Of Modules	1 module
Socket Number	1
Type Of Footprint	Infraplus
Connector Type	S-One
Cable Shielding Type	U/UTP
Organization Of Wire	Unshielded twisted pair
Connections - Terminals	Click
Fixing Mode	Clip-in
Installation Direction	Straight
Material	ASA + PC: mechanism cover
Depth	36 mm
Width	22.5 mm
Height	45 mm
Embedding Depth	25 mm

### Environment

Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK01
Ambient Air Temperature For Operation	15...30 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Storage	0...35 °C
Environmental Characteristic	Petrol Acetone Window-cleaning fluid UV resistant Oil Bleach Alcohol Liquid soap
Standards	ISO 8877

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.1 cm
Package 1 Width	6.1 cm
Package 1 Length	7.4 cm
Package 1 Weight	20 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	5.6 cm
Package 2 Width	11.4 cm
Package 2 Length	24.6 cm
Package 2 Weight	252 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	300
Package 3 Height	30 cm
Package 3 Width	40 cm
Package 3 Length	60 cm
Package 3 Weight	8.263 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability




**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	<a href="#">Yes</a>
<b>Reach Regulation</b>	<a href="#">REACH Declaration</a>	
<b>Eu Rohs Directive</b>	Compliant	<a href="#">EU RoHS Declaration</a>
<b>China Rohs Regulation</b>	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)	
<b>Weee</b>	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
<b>Circularity Profile</b>	No need of specific recycling operations	