

Product data sheet

Specifications



Unica - 1 RJ45 socket (S-One) - 2 m - Cat.6, FTP - ivory

MGU3.427.25

⚠ Discontinued on: Jun 15, 2023

⚠ Discontinued

Main

Range	Unica
Aesthetic Name	Unica (standard aesthetic)
Product Or Component Type	Data socket
Device Presentation	Mechanism
Colour Tint	Ivory (RAL 9010)
Data Socket Type	RJ45 8 contact(s) Cat.6 < 250 MHz
Provided Equipment	Label holder Protective flap

Complementary

Communication Network Type	1000BASE-TX
Communication Port Protocol	ATM 1200 Mbps
Number Of Modules	2 modules
Socket Number	1
Type Of Footprint	Infraplus
Connector Type	S-One
Cable Shielding Type	U/FTP
Organization Of Wire	Shielded twisted pair
Connections - Terminals	Click
Fixing Mode	Clip-in
Installation Direction	Straight
Material	ASA + PC: mechanism cover
Depth	36 mm
Width	85 mm
Height	80 mm
Embedding Depth	25 mm
Net Weight	0.033 kg

Environment

Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK01

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	15...30 °C
Ambient Air Temperature For Storage	0...35 °C
Environmental Characteristic	Acetone Window-cleaning fluid Petrol Bleach Liquid soap Alcohol UV resistant Oil
Standards	ISO 8877

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.2 cm
Package 1 Width	4.65 cm
Package 1 Length	4.65 cm
Package 1 Weight	16.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	33.5 cm
Package 2 Width	4.4 cm
Package 2 Length	13.6 cm
Package 2 Weight	160.0 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations