

# Product data sheet

Specifications



## Unica - USB data connector - 1 module - ivory

MGU3.429.25

 **Discontinued on:** Jun 15, 2023

 **Discontinued**

### Main

Range	Unica
Product Or Component Type	USB connector
Connector Type	USB 2.0
Electrical Circuit Type	Data
Device Presentation	Mechanism
Colour Tint	Ivory (RAL 9010)
Type Of Packing	Group

### Complementary

Device Mounting	Flush
Socket Number	1
Fixing Mode	Clip-in
Number Of Modules	1 module
Surface Finish	Matt
Quantity Per Set	Set of 10
Connections - Terminals	Screw terminals
Clamping Connection Capacity	<= 1.5 mm² for stranded cable(s) <= 1.5 mm² for flexible cable(s) <= 1.5 mm² for rigid cable(s)
Wire Stripping Length	8 mm
Material	Thermoplastic ABS-UV stabilised: centre plate PC (polycarbonate) GF10 FR: casing
Height	45 mm
Width	22.5 mm
Depth	28.3 mm
Embedding Depth	19.7 mm
Net Weight	0.0141 kg

### Environment

Ambient Air Temperature For Storage	-5...50 °C
Ambient Air Temperature For Operation	-5...40 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 998-2-1 IEC 998-1
Ip Degree Of Protection	IP21
Ik Degree Of Protection	IK04
Environmental Characteristic	UV resistant Window-cleaning fluid Oil Acetone Petrol Bleach Alcohol Liquid soap

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.2 cm
Package 1 Width	2.8 cm
Package 1 Length	4.8 cm
Package 1 Weight	40.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	5.0 cm
Package 2 Width	10.5 cm
Package 2 Length	23.7 cm
Package 2 Weight	400.0 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	20
Package 3 Height	15.0 cm
Package 3 Width	15.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	1.03 kg

## Sustainability




**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	<a href="#">Yes</a>
<hr/>		
Eu Rohs Directive		Compliant <a href="#">EU RoHS Declaration</a>
<hr/>		
China Rohs Regulation		<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
<hr/>		