

Product data sheet

Specifications



Unica - 1 RJ45 socket (S-One) - 1 m - Cat.6_A, S/FTP - ivory

MGU3.446.25

 **Discontinued on:** Sep 30, 2023

 **Discontinued**

Main

Range	Unica
Aesthetic Name	Unica (standard aesthetic)
Product Or Component Type	Data socket
Device Presentation	Mechanism
Colour Tint	Ivory (RAL 9010)
Data Socket Type	RJ45 8 contact(s) Cat.6 _A < 500 MHz
Provided Equipment	Protective flap Label holder

Complementary

Communication Network Type	10GBASE-T
Communication Port Protocol	ATM 1200 Mbps
Number Of Modules	1 module
Socket Number	1
Type Of Footprint	Infraplus
Connector Type	S-One
Cable Shielding Type	S/FTP
Organization Of Wire	Shielded twisted pair
Connections - Terminals	Click
Fixing Mode	Clip-in
Installation Direction	Straight
Material	ASA + PC: mechanism cover
Depth	36 mm
Width	22.5 mm
Height	45 mm
Embedding Depth	25 mm

Environment

Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK01
Ambient Air Temperature For Operation	15...30 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Storage	0...35 °C
Environmental Characteristic	Acetone Liquid soap UV resistant Alcohol Petrol Oil Bleach Window-cleaning fluid
Standards	ISO 8877

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.3 cm
Package 1 Width	4.6 cm
Package 1 Length	4.2 cm
Package 1 Weight	40.0 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Reach Free Of Svhc	
 Toxic Heavy Metal Free	
 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins