

# Product data sheet

Specifications



## Unica - rotary dimmer - 230 VAC - 40...400 W/VA - white

MGU3.511.18

 **Discontinued on:** Feb 29, 2024

 **Discontinued**

### Main

Aesthetic Name	Unica (standard aesthetic)
Product Or Component Type	Dimmer
Device Presentation	Mechanism
Fixing Mode	Clip-in
[Ue] Rated Operational Voltage	230 V AC 50 Hz
Number Of Modules	2 modules
Colour Tint	White (RAL 9003)

### Complementary

Dimmer Control	Rotary push type
Maximum Permanent Current	1.74 A
Total Number Of Wires	2
Load Type	230 V AC halogen lamp - 40...400 W 230 V AC incandescent lamp - 40...400 W Low voltage halogen lamp with ferromagnetic transformer - 40...400 VA
Protection Type	Fuse protection
Fuse Type	4 Ah 5 x 20 mm 230 V 50 Hz
Marking	L+N
Connections - Terminals	Screw terminals
Clamping Connection Capacity	<= 2 x 2.5 mm <sup>2</sup>
Connected Auxiliaries	2-way switch
Material	ASA + PC: mechanism cover
Standards	EN 60669-2-1
Product Certifications	CE
Ambient Air Temperature For Operation	5...30 °C
Ambient Air Temperature For Storage	-20...60 °C
Embedding Depth	34 mm
Depth	54 mm
Width	45 mm
Height	45 mm
Net Weight	0.071 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

<b>Ik Degree Of Protection</b>	IK01
<b>Ip Degree Of Protection</b>	IP20
<b>Environmental Characteristic</b>	Acetone Liquid soap Petrol UV resistant Oil Alcohol Bleach Window-cleaning fluid

## Packing Units

<b>Unit Type Of Package 1</b>	PCE
<b>Number Of Units In Package 1</b>	1
<b>Package 1 Height</b>	6.400 cm
<b>Package 1 Width</b>	9.800 cm
<b>Package 1 Length</b>	10.800 cm
<b>Package 1 Weight</b>	125.000 g
<b>Unit Type Of Package 2</b>	S02
<b>Number Of Units In Package 2</b>	15
<b>Package 2 Height</b>	15.000 cm
<b>Package 2 Width</b>	30.000 cm
<b>Package 2 Length</b>	40.000 cm
<b>Package 2 Weight</b>	2.200 kg

## Contractual warranty

<b>Warranty</b>	18 months
-----------------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



## Transparency

Eu Rohs Directive	Under investigation
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>