

Product data sheet

Specifications



Unica Wireless - combined relay - 230 VAC - 0...2300 W - 2 m - graphite

MGU3.572.12

 **Discontinued on:** Dec 15, 2021

 **Discontinued**

Main

Range Of Product	Unica Wireless
Product Or Component Type	Combined relay
Device Presentation	Mechanism
Transmission Frequency	868 MHz
[Ue] Rated Operational Voltage	110/230 V AC +/- 10 % at 50/60 Hz
Number Of Modules	2 modules
Fixing Mode	Clip-in
Colour Tint	Graphite
Device Composition	1 large rocker and 2 narrow rockers Wireless emitter and receiver
Provided Equipment	Set of 8 symbols

Complementary

Wiring Device Mounting	Flush
Operating Distance	10...50 m indoor <= 300 m outdoor
Load Type	230 V AC compact fluorescent lamp - 880 VA 230 V AC fan - 690 W 230 V AC halogen lamp - 2000 W 230 V AC incandescent lamp - 2300 W 230 V AC LED lamp - 880 W Fluorescent tube (diameter: 28...38 mm): 1 1-10 V dimmable electronic ballast - 920 VA Low voltage halogen lamp with electronic transformer - 500 VA Low voltage halogen lamp with ferromagnetic transformer - 500 VA Low voltage halogen lamp with toroidal transformer - 500 VA Motor - 690 W
Protection Type	Fuse protection
Connections - Terminals	Screw terminals
Clamping Connection Capacity	<= 2 x 2.5 mm ² for flexible cable(s) <= 2 x 2.5 mm ² for rigid cable(s)
Type Of Setting	Neutral position

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	EN 61000-6-3 ETSI EN 301 489 ETSI EN 300 220 EN 60669-1 EN 60669-2-1 99/5/EEC EN 61000-6-2 89/336/EEC 73/23/EEC
Ambient Air Temperature For Operation	-5...50 °C
Relative Humidity	20...95 %
Embedding Depth	34 mm
Depth	46 mm

Environment

Ip Degree Of Protection	IP20
Environmental Characteristic	Bleach Alcohol Window-cleaning fluid Oil Petrol Liquid soap Acetone UV resistant

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.3 cm
Package 1 Width	10 cm
Package 1 Length	10.9 cm
Package 1 Weight	128 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Eu Rohs Directive	Compliant
	EU RoHS Declaration

China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)

Environmental Disclosure	Product Environmental Profile
---------------------------------	---

Circularity Profile	End of Life Information
----------------------------	---