

Product data sheet

Specifications



Unica Wireless - combined dimmer without neutral - 230 VAC - 2 m - white

MGU3.573.18

 **Discontinued on:** Dec 15, 2021

 **Discontinued**

Main

Range Of Product	Unica Wireless
Product Or Component Type	Combined dimmer
Device Presentation	Mechanism
Transmission Frequency	868.3 MHz
[Ue] Rated Operational Voltage	230 V AC +/- 10 % at 50 Hz
Number Of Modules	2 modules
Fixing Mode	Clip-in
Colour Tint	White
Device Composition	1 large rocker and 2 narrow rockers Wireless emitter and receiver
Provided Equipment	Set of 8 symbols

Complementary

Wiring Device Mounting	Flush
Type Of Setting	Without neutral position
Operating Distance	10...50 m indoor <= 300 m outdoor
Load Type	230 V AC halogen lamp - 20...315 W 230 V AC incandescent lamp - 20...315 W Low voltage halogen lamp with electronic transformer - 20...315 VA Low voltage halogen lamp with ferromagnetic transformer - 20...315 VA Low voltage halogen lamp with toroidal transformer - 20...270 VA
Protection Type	Damage protection from inappropriate load Overload protection Temperature rise protection Short-circuit protection
Connections - Terminals	Screw terminals
Clamping Connection Capacity	<= 2 x 2.5 mm ² for flexible cable(s) <= 2 x 2.5 mm ² for rigid cable(s)
Standards	EN 61000-6-3 99/5/EEC EN 61000-6-2 89/336/EEC ETSI EN 301 489 ETSI EN 300 220 EN 60669-2-1 73/23/EEC EN 60669-1
Ambient Air Temperature For Operation	-5...35 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Relative Humidity	20...95 %
Embedding Depth	34 mm
Depth	46 mm

Environment

Ip Degree Of Protection	IP20
Environmental Characteristic	Acetone Window-cleaning fluid Alcohol Liquid soap Petrol Oil Bleach UV resistant

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.3 cm
Package 1 Width	9.8 cm
Package 1 Length	10.8 cm
Package 1 Weight	132 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins