

Product data sheet

Specifications



Unica Wireless - combined roller blind - 230 VAC - 0...690 W - 2 m - graphite

MGU3.574.12

 **Discontinued on:** Jun 15, 2023

 **Discontinued**

Main

| | |
|--------------------------------|--|
| Range Of Product | Unica Wireless |
| Product Or Component Type | Combined roller blind |
| Device Presentation | Mechanism |
| Transmission Frequency | 868.3 MHz |
| [Ue] Rated Operational Voltage | 110/230 V AC +/- 10 % at 50/60 Hz |
| Number Of Modules | 2 modules |
| Fixing Mode | Claws |
| Colour Tint | Graphite |
| Device Composition | Wireless emitter and receiver 1 large rocker and 2 narrow rockers |
| Provided Equipment | Set of 4 symbols |

Complementary

| | |
|---------------------------------------|---|
| Wiring Device Mounting | Flush |
| Operating Distance | 10...50 m indoor <= 300 m outdoor |
| Load Type | Motor: 690 W |
| Protection Type | Fuse protection |
| Connections - Terminals | Screw terminals |
| Clamping Connection Capacity | <= 2 x 2.5 mm ² for flexible cable(s) <= 2 x 2.5 mm ² for rigid cable(s) |
| Type Of Setting | Neutral position |
| Standards | EN 60669-2-1 ETSI EN 300 220 EN 60669-1 89/336/EEC 99/5/EEC ETSI EN 301 489 |
| Ambient Air Temperature For Operation | -5...50 °C |
| Relative Humidity | 20...95 % |
| Embedding Depth | 34 mm |
| Depth | 46 mm |

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|---|
| Ip Degree Of Protection | IP20 |
| Environmental Characteristic | Acetone Petrol Alcohol Window-cleaning fluid Bleach Liquid soap UV resistant Oil |

Packing Units

| | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 6.6 cm |
| Package 1 Width | 10.1 cm |
| Package 1 Length | 10.8 cm |
| Package 1 Weight | 129.0 g |
| Unit Type Of Package 2 | S03 |
| Number Of Units In Package 2 | 34 |
| Package 2 Height | 30.0 cm |
| Package 2 Width | 30.0 cm |
| Package 2 Length | 40.0 cm |
| Package 2 Weight | 4.873 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Well-being performance

| | |
|------------------------------|---|
| ✓ Toxic Heavy Metal Free | |
| ✓ Mercury Free | |
| ✓ Rohs Exemption Information | Yes |
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | End of Life Information |