

Product data sheet

Specifications



Unica - rotary selector switch - 4 pos. - 32 A 250 VAC - 2 m - ivory

MGU3.579.25

⚠ Discontinued on: Jun 15, 2023

⚠ Discontinued

Main

Range Of Product	Unica
Aesthetic Name	Unica (standard aesthetic)
Product Or Component Type	Selector switch
Device Presentation	Mechanism
Technology Type	Electromechanical
Switch Function	4 positions
Device Application	Light control
Colour Tint	Ivory

Complementary

Rated Current	32 A
[Ue] Rated Operational Voltage	250 V
Network Type	AC
Network Frequency	50/60 Hz
Power Range	40...300 W 40...300 VA
Electrical Durability	10000 cycles, cos phi = 0.6
Insulation Resistance	> 5 MOhm at 500 V
Dielectric Strength	2000 V
Minimum Load Breaking Capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Opening Distance	> 3 mm
Actuator	Rotary
Number Of Modules	2 modules
Connections - Terminals	Screw terminals
Cable Cross Section	0...6 mm² flexible cable 0...6 mm² rigid cable
Material	ASA + PC: mechanism cover
Marking	1
Fixing Mode	Clip-in
Width	45 mm
Height	45 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Depth	30 mm
Net Weight	0.027 kg
Ambient Air Temperature For Operation	25...35 °C
Ambient Air Temperature For Storage	0...50 °C
Standards	EMC directive LV directive EN 60669-1

Environment

Ip Degree Of Protection	IP20
Ik Degree Of Protection	IK01
Environmental Characteristic	Liquid soap UV resistant Acetone Alcohol Petrol Window-cleaning fluid Oil Bleach

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.7 cm
Package 1 Width	4.8 cm
Package 1 Length	6.8 cm
Package 1 Weight	29.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	33.5 cm
Package 2 Width	4.4 cm
Package 2 Length	13.6 cm
Package 2 Weight	290.0 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations