


# Product data sheet

Specifications



## Unica - RCD switch - 1P+N - 6 A, 230 VAC - 2 m - white

MGU3.610.18

 **Discontinued on:** Sep 18, 2015

 **Discontinued**

### Main

Range	Unica
Device Application	Control
Product Or Component Type	Residual current device switch
Aesthetic Name	Unica (standard aesthetic)
Device Presentation	Mechanism
Poles Description	1P + N
Rated Current	6 A at 230 V AC
Number Of Modules	2 modules
Fixing Mode	Clip-in
Cover Plate Colour Tint	White

### Complementary

Marking	I-O
Connections - Terminals	Screw terminals
Clamping Connection Capacity	<= 2 x 2.5 mm <sup>2</sup> for flexible cable(s) <= 2 x 2.5 mm <sup>2</sup> for rigid cable(s)
Trip Unit Technology	Thermal-magnetic
Breaking Capacity	1.5 kA
Earth-Leakage Sensitivity	10 mA
Earth-Leakage Protection Class	Class A
Material	ASA + PC: mechanism cover
Standards	EN 61009
Ambient Air Temperature For Operation	-5...40 °C
Ambient Air Temperature For Storage	0...50 °C
Embedding Depth	38 mm
Depth	54 mm
Width	45 mm
Height	45 mm
Net Weight	0.089 kg

### Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

<b>Ik Degree Of Protection</b>	IK01
<b>Ip Degree Of Protection</b>	IP41
<b>Environmental Characteristic</b>	Oil Window-cleaning fluid Bleach Liquid soap Petrol Acetone Alcohol

## Packing Units

<b>Unit Type Of Package 1</b>	PCE
<b>Number Of Units In Package 1</b>	1
<b>Package 1 Height</b>	5.8 cm
<b>Package 1 Width</b>	7.5 cm
<b>Package 1 Length</b>	7.5 cm
<b>Package 1 Weight</b>	115 g

## Contractual warranty

<b>Warranty</b>	18 months
-----------------	-----------