

Product data sheet

Specifications



Unica - fuse holder - 10 A, 250 VAC - cyl. 6x32 mm - 1 m - ivory

MGU3.630.25

⚠ Discontinued on: Feb 27, 2018

⚠ End-of-service on: Mar 13, 2018

⚠ Discontinued

Main

Range	Unica
Device Application	Safety
Product Or Component Type	Fuse holder
Aesthetic Name	Unica (standard aesthetic)
Device Presentation	Mechanism
Rated Current	10 A
[Ue] Rated Operational Voltage	230 V
Network Type	AC
Network Frequency	50/60 Hz
Number Of Modules	1 module
Fixing Mode	Clip-in
Colour Tint	Ivory

Complementary

Fuse Type	Cylindrical 6 x 32 mm
Provided Equipment	Fuse not supplied
Connections - Terminals	Screw terminals
Cable Cross Section	0...4 mm² flexible cable 0...4 mm² rigid cable
Material	ASA + PC: mechanism cover
Standards	EN 60127-6
Product Certifications	ES.ME01.B02318 AC
Ambient Air Temperature For Operation	15...30 °C
Ambient Air Temperature For Storage	0...35 °C
Embedding Depth	31 mm
Depth	44 mm
Width	22.5 mm
Height	45 mm
Net Weight	0.0278 kg

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ik Degree Of Protection	IK01
Ip Degree Of Protection	IP20
Environmental Characteristic	Petrol Bleach Alcohol Oil Liquid soap UV resistant Acetone Window-cleaning fluid

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.7 cm
Package 1 Width	4.4 cm
Package 1 Length	6.8 cm
Package 1 Weight	38 g

Contractual warranty

Warranty	18 months
-----------------	-----------