

# Product data sheet

Specifications



## Unica - electronic bell - 230V AC - 2 m - clip-in - white

MGU3.786.18

 **Discontinued on:** Feb 21, 2024

 **Discontinued**

### Main

Range	Unica
Device Application	Signalling
Product Or Component Type	Electronic doorbell
Aesthetic Name	Unica (standard aesthetic)
Device Presentation	Mechanism
[Ue] Rated Operational Voltage	230 V AC 50/60 Hz
Number Of Modules	2 modules
Fixing Mode	Clip-in
Colour Tint	White (RAL 9003)

### Complementary

Current Consumption	14 mA
Type Of Setting	5 programmable melodies
Device Mounting	Flush
Connections - Terminals	Screw terminals
Acoustic Level	70 dB/1m
Cable Cross Section	0.75...1.5 mm <sup>2</sup> flexible cable 0.75...1.5 mm <sup>2</sup> rigid cable
Connected Auxiliaries	10 standard push-buttons connected in parallel 3 indicator lights connected in parallel
Material	ASA + PC: mechanism cover
Standards	IEC 62080
Product Certifications	CE
Ambient Air Temperature For Operation	15...30 °C
Ambient Air Temperature For Storage	0...35 °C
Embedding Depth	33 mm
Depth	44 mm
Width	45 mm
Height	45 mm
Net Weight	0.11 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

<b>Ik Degree Of Protection</b>	IK01
<b>Ip Degree Of Protection</b>	IP20
<b>Environmental Characteristic</b>	Window-cleaning fluid Acetone UV resistant Bleach Oil Liquid soap Alcohol Petrol

## Packing Units

<b>Unit Type Of Package 1</b>	PCE
<b>Number Of Units In Package 1</b>	1
<b>Package 1 Height</b>	6.0 cm
<b>Package 1 Width</b>	8.0 cm
<b>Package 1 Length</b>	8.5 cm
<b>Package 1 Weight</b>	141.0 g
<b>Unit Type Of Package 2</b>	S01
<b>Number Of Units In Package 2</b>	9
<b>Package 2 Height</b>	15 cm
<b>Package 2 Width</b>	15 cm
<b>Package 2 Length</b>	40 cm
<b>Package 2 Weight</b>	1.427 kg
<b>Unit Type Of Package 3</b>	P06
<b>Number Of Units In Package 3</b>	288
<b>Package 3 Height</b>	75 cm
<b>Package 3 Width</b>	80 cm
<b>Package 3 Length</b>	60 cm
<b>Package 3 Weight</b>	53.664 kg

## Contractual warranty

<b>Warranty</b>	18 months
-----------------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations