

Product data sheet

Specifications



Unica Top/Class - electronic bell - 230V AC - 2 m - clip-in - aluminium

MGU3.786.30

⚠ Discontinued on: Dec 31, 2023

⚠ Discontinued

Main

Range	Unica
Device Application	Signalling
Product Or Component Type	Electronic doorbell
Aesthetic Name	Unica Top - Unica Class
Device Presentation	Mechanism
[Ue] Rated Operational Voltage	230 V AC 50/60 Hz
Number Of Modules	2 modules
Fixing Mode	Clip-in
Colour Tint	Aluminium

Complementary

Current Consumption	14 mA
Type Of Setting	5 programmable melodies
Device Mounting	Flush
Connections - Terminals	Screw terminals
Acoustic Level	70 dB/1m
Cable Cross Section	0.75...1.5 mm² flexible cable 0.75...1.5 mm² rigid cable
Connected Auxiliaries	3 indicator lights connected in parallel 10 standard push-buttons connected in parallel
Material	ASA + PC: mechanism cover
Standards	IEC 62080
Product Certifications	CE
Ambient Air Temperature For Operation	15...30 °C
Ambient Air Temperature For Storage	0...35 °C
Embedding Depth	33 mm
Depth	44 mm
Width	45 mm
Height	45 mm
Net Weight	0.11 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

<hr/>	
Ik Degree Of Protection	IK01
<hr/>	
Ip Degree Of Protection	IP20
<hr/>	
Environmental Characteristic	Liquid soap Alcohol Acetone Window-cleaning fluid UV resistant Petrol Bleach Oil

Packing Units

<hr/>	
Unit Type Of Package 1	PCE
<hr/>	
Number Of Units In Package 1	1
<hr/>	
Package 1 Height	6.5 cm
<hr/>	
Package 1 Width	7.5 cm
<hr/>	
Package 1 Length	8.5 cm
<hr/>	
Package 1 Weight	146.0 g

Contractual warranty

<hr/>	
Warranty	18 months

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations