

# Product data sheet

Specifications



## Unica - key card switch - 10 A - 230 VAC - 2 m - white

MGU5.283.18ZD

 **Discontinued on:** Dec 30, 2021

 **Discontinued**

### Main

Range	Unica
Aesthetic Name	Unica (standard aesthetic)
Product Or Component Type	Card switch
Device Application	Control
Device Presentation	Mechanism with fixing frame
Colour Tint	White (RAL 9003)

### Complementary

Technology Type	Electronic
[Ue] Rated Operational Voltage	230 V AC +/- 10 % at 50 Hz
Rated Current	10 A
Load Type	230 V AC incandescent lamp - 1470 W 230 V AC halogen lamp - 1470 W 230 V AC fan - 1470 W 230 V AC convector - 1470 W Low voltage halogen lamp with ferromagnetic transformer - 1000 VA Low voltage halogen lamp with electronic transformer - 1470 VA Fluorescent tube ferromagnetic ballast - 1470 VA Compact fluorescent lamp - 1470 W LED lamp - 1470 W Contactor
Condition Of Use	Control through appropriate relay
Actuator	Card 54 x 86 x 0.85 mm (maximum)
Number Of Modules	2 modules
Maximum Number Of Switchings	50000 operations
Pilot Light	locator lamp
Marking	Vertical insertion pictogram
Connections - Terminals	Soldered connectors
Clamping Connection Capacity	<= 1 x 2.5 mm <sup>2</sup> for flexible cable(s) <= 1 x 2.5 mm <sup>2</sup> for rigid cable(s)
Fixing Mode	Screws
Material	ASA + PC: mechanism cover Zamak: fixing frame
Surface Finish	Untreated
Embedding Depth	14 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Depth	Unica Basic cover frame: 36 mm Unica Colors cover frame: 36 mm Unica Allegro cover frame: 35 mm Unica Plus cover frame: 35 mm
Width	70.9 mm
Height	70.9 mm
Net Weight	0.0645 kg

## Environment

Ip Degree Of Protection	IP20
Ik Degree Of Protection	IK01
Ambient Air Temperature For Operation	5...30 °C
Ambient Air Temperature For Storage	-20...60 °C
Environmental Characteristic	Acetone Alcohol Window-cleaning fluid Liquid soap Petrol UV resistant Oil Bleach
Product Certifications	FR ME63 B02736
Standards	EN 61058-1

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	7.5 cm
Package 1 Length	7.5 cm
Package 1 Weight	58 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations