

Product data sheet

Specifications



Unica KNX - room temperature control unit - 230 VAC - 2 m - graphite

MGU50.534.12

⚠ Discontinued on: Dec 31, 2017

⚠ Discontinued

Main

Range	Unica
Aesthetic Name	Unica KNX
Product Or Component Type	Thermostat
Device Application	Room
Device Presentation	Mechanism with fixing frame
Colour Tint	Graphite

Complementary

Technology Type	Electronic
[Ue] Rated Operational Voltage	230 V AC +/- 10 % at 50/60 Hz
Number Of Modules	2 modules
Device Composition	Display 4 buttons
Clamping Connection Capacity	<= 2 x 2.5 mm ² for flexible cable(s) <= 2 x 2.5 mm ² for rigid cable(s)
Contacts Type And Composition	1 C/O
Connections - Terminals	Screwless terminals
Information Displayed	Day Operating mode Temperature Time
Status Led	Programming LED
Programmable Temperature	No
Temperature Setting Range	0...40 °C
Measurement Accuracy	± 1 K
Fixing Mode	Long claws
Minimum Mounting Height	1.5 m
Depth	39 mm
Embedding Depth	26 mm

Environment

Ip Degree Of Protection	IP20
Ik Degree Of Protection	IK01

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	-5...45 °C
Environmental Characteristic	Petrol Acetone Alcohol Window-cleaning fluid Bleach Liquid soap Oil UV resistant
Standards	EMC directive LV directive

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8 cm
Package 1 Width	9.5 cm
Package 1 Length	9.5 cm
Package 1 Weight	0.172 kg

Contractual warranty

Warranty	18 months
----------	-----------