

Product data sheet

Specifications



Unica Plus - 2 complete S.O. - 2P+E, CZ - 4 m - ivory/light grey

MGU63.065.524D

⚠ Discontinued on: Dec 17, 2020

⚠ Discontinued

Main

Range	Unica
Product Or Component Type	Socket-outlet
Aesthetic Name	Unica Plus
Device Presentation	Complete mechanism
Device Mounting	Flush
Socket Number	2
Outlet Poles Configuration	2P + E
Outlet Standard	Slovakia Czech Republic
Outlet Standard Description	Pin earth
Socket Additional Information	In pin pack
Rated Current	16 A

Complementary

Device Application	Power supply
[Ue] Rated Operational Voltage	250 V
Network Type	AC
Network Frequency	50/60 Hz
Number Of Modules	4 modules
Fixing Mode	2 pins
Colour Tint	Ivory
Connections - Terminals	Screw terminals
Cable Cross Section	0...4 mm ² - cable stiffness: flexible 0...4 mm ² - cable stiffness: rigid
Minimum Load Breaking Capacity	100 operations 1.25 In and 1.1 Un, cos phi = 0.6
Electrical Durability	10000 cycles, cos phi = 0.8
Insulation Resistance	> 5 MOhm at 500 V
Dielectric Strength	2000 V
Material	ASA + PC: mechanism cover ABS (acrylonitrile butadiene-styrene): cover frame
Quantity Per Set	Set of 1 plastic bag and cardboard with eurohole
Embedding Depth	27 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Depth	37 mm
Width	90.21 mm
Height	122.9 mm
Net Weight	0.1153 kg

Environment

Ambient Air Temperature For Operation	15...30 °C
Ambient Air Temperature For Storage	0...35 °C
Ik Degree Of Protection	IK01
Ip Degree Of Protection	IP20
Environmental Characteristic	Window-cleaning fluid Alcohol Liquid soap Oil Acetone UV resistant Bleach Petrol

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.25 cm
Package 1 Width	9 cm
Package 1 Length	4.75 cm
Package 1 Weight	119 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations