

# Product data sheet

Specifications



## Mini Pragma surface enclosure - IP 40 - 1 x 18 modules - smoked transparent door

MIP02118T

⚠ Discontinued on: Sep 13, 2019

⚠ Discontinued

### Main

|                             |                   |
|-----------------------------|-------------------|
| Range                       | Mini Pragma       |
| Product Or Component Type   | Enclosure         |
| Enclosure Type              | Modular enclosure |
| Nb Of 18 Mm Modules Per Row | 18                |
| Nb Of Horizontal Rows       | 1                 |
| Type Of Door                | Transparent door  |
| Width                       | 376 mm outside:   |
| Height                      | 228 mm outside:   |
| Depth                       | 103 mm outside:   |

### Complementary

|                               |  |
|-------------------------------|--|
| Enclosure Mounting            | Surface  |
| 9 Mm Pitches                  | 36   |
| Total Number Of 18 Mm Modules | 18   |
| [In] Rated Current            | 63 A   |
| Type Of Rail                  | 35 mm asymmetrical rail  |
| Cable Entry                   | 1 bare flange<br>1 trunking flange   |
| Terminal Block Function       | Earth / neutral  |
| Number Of Terminal Blocks     | 1 earth (screwed) with 16 outgoing<br>1 neutral (screwed) with 16 outgoing   |
| Distribution Block Outgoers   | 2 x 16 mm² for earth<br>2 x 16 mm² for neutral<br>6 x 6 mm² for earth<br>6 x 6 mm² for neutral<br>8 x 10 mm² for earth<br>8 x 10 mm² for neutral |
| Enclosure Material            | Back part: technoplastic<br>Door: technoplastic<br>Front face: technoplastic   |
| Colour                        | Front face: white<br>Door: smoked  |

### Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                                       |   |
|---------------------------------------|---|
| Standards                             | IEC 61439-1<br>IEC 61439-3<br>IEC 60670-1<br>IEC 60670-24 |
| Quality Labels                        | IMQ   |
| Fire Resistance                       | Back part: 750 °C<br>Door: 650 °C<br>Front face: 750 °C   |
| Ik Degree Of Protection               | IK07  |
| Ambient Air Temperature For Operation | -25...60 °C   |

## Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type Of Package 1       | PCE     |
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 10.3 cm |
| Package 1 Width              | 37.6 cm |
| Package 1 Length             | 22.8 cm |
| Package 1 Weight             | 1.1 kg  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|