

Product data sheet

Specifications



mini Pragma surface enclosure - 2 x 12 modules - smoked door

MIP11212S

⚠ Discontinued on: Mar 23, 2020

⚠ Discontinued

Main

Range	Mini Pragma
Product Or Component Type	Enclosure
Enclosure Type	Modular enclosure
Nb Of 18 Mm Modules Per Row	12
Nb Of Horizontal Rows	2
Type Of Door	Smoked
Width	268 mm outside:
Height	353 mm outside:
Depth	102 mm outside:

Complementary

Enclosure Mounting	Surface
9 Mm Pitches	24
Total Number Of 18 Mm Modules	24
[In] Rated Current	63 A
Type Of Rail	35 mm asymmetrical rail
Cable Entry	1 bare flange 1 trunking flange
Terminal Block Function	Earth
Number Of Terminal Blocks	1 earth (screwed) with 16 outgoers
Distribution Block Outgoers	2 x 16 mm ² for earth 6 x 6 mm ² for earth 8 x 10 mm ² for earth
Enclosure Material	Back part: technoplastic Door: technoplastic Front face: technoplastic
Colour	Door: smoked Front face: white (RAL 9003)

Environment

Standards	IEC 61439-1 IEC 61439-3 IEC 60670-1 IEC 60670-24
Quality Labels	IMQ

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Fire Resistance	Back part: 750 °C Door: 650 °C Front face: 750 °C
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07
Ambient Air Temperature For Operation	-25...60 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10 cm
Package 1 Width	26.8 cm
Package 1 Length	35.2 cm
Package 1 Weight	1.134 kg

Contractual warranty

Warranty	18 months
----------	-----------