

# Product data sheet

Specifications



Enclosure, Resi9 MP, flush mounting, 1 row of 4 modules, IP40, white door, no terminal block

MIP20104

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

## Main

Range	Resi9
Product Name	Resi9 MP
Product Or Component Type	Enclosure
Enclosure Type	Modular enclosure
Nb Of 18 Mm Modules Per Row	4
Nb Of Horizontal Rows	1
Type Of Door	Plain
Width	126 mm wall: 150 mm outside:
Height	228 mm wall: 252 mm outside:
Depth	18 mm outside: 80 mm wall: 98 mm total:

## Complementary

Enclosure Mounting	Flush
9 Mm Pitches	8
Total Number Of 18 Mm Modules	4
[In] Rated Current	50 A
Type Of Rail	35 mm asymmetrical rail
Mounting Plate Description	Without mounting plate
Cable Entry	Pre-cutted holes
Terminal Block Function	Without
Enclosure Material	Back part: technoplastic Door: technoplastic Front face: technoplastic
Internal Depth	76 mm
Colour	Door: white (RAL 9003) Front face: white (RAL 9003)
Market Segment	Residential

## Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications



Standards	IEC 61439-1 IEC 61439-3 IEC 60670-1 IEC 60670-24
Quality Labels	IMQ
Fire Resistance	Door: 650 °C Back part: 650 °C Front face: 650 °C
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07
Ambient Air Temperature For Operation	-25...60 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.7 cm
Package 1 Width	15 cm
Package 1 Length	25.2 cm
Package 1 Weight	400 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	15
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	52 cm
Package 2 Weight	6.1 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	120
Package 3 Height	60 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	60.8 kg

## Contractual warranty

Warranty	18 months
----------	-----------



# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

✓ Halogen Free Product

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations