

Product data sheet

Specifications



mini Pragma recessed enclosure - 1 x 8 modules - smoked door

MIP21108S

 **Discontinued on:** Mar 23, 2020

 **Discontinued**

Main

Range	Mini Pragma
Product Or Component Type	Enclosure
Enclosure Type	Modular enclosure
Nb Of 18 Mm Modules Per Row	8
Nb Of Horizontal Rows	1
Type Of Door	Smoked
Width	198 mm wall: 222 mm outside:
Height	228 mm wall: 252 mm outside:
Depth	18 mm outside: 80 mm wall: 98 mm total:

Complementary

Enclosure Mounting	Flush
9 Mm Pitches	16
Total Number Of 18 Mm Modules	8
[In] Rated Current	63 A
Type Of Rail	35 mm asymmetrical rail
Cable Entry	Pre-cutted holes
Terminal Block Function	Earth
Number Of Terminal Blocks	1 earth (screwed) with 8 outgoers
Distribution Block Outgoers	1 x 16 mm ² for earth 3 x 6 mm ² for earth 4 x 10 mm ² for earth
Enclosure Material	Back part: technoplastic Door: technoplastic Front face: technoplastic
Colour	Door: smoked Front face: white (RAL 9003)

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 61439-1 IEC 61439-3 IEC 60670-1 IEC 60670-24
Quality Labels	IMQ
Fire Resistance	Door: 650 °C Front face: 750 °C Back part: 850 °C
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07
Ambient Air Temperature For Operation	-25...60 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.6 cm
Package 1 Width	22.5 cm
Package 1 Length	25.5 cm
Package 1 Weight	0.703 kg

Contractual warranty

Warranty	18 months
----------	-----------