

Product data sheet

Specifications



Front face, Resi9 MP, 3 rows of 12 modules, plain

MIP30312

Main

| | |
|------------------------------------|------------------------|
| Range | Resi9 |
| Product Or Component Type | Front face |
| Type Of Front Plate | Plain |
| Accessory / Separate Part Category | Installation accessory |
| Range Compatibility | Resi9 Resi9 MP |

Complementary

| | |
|---------------------------------|--|
| Enclosure Mounting | Flush |
| Type Of Front Cover | Plain |
| Number Of Horizontal Rows | 3 |
| Number Of 18 Mm Modules Per Row | 12 |
| Total Number Of 18 Mm Modules | 36 |
| Enclosure Material | Door: technoplastic Front face: technoplastic |
| Width | 294 mm outside: |
| Height | 502 mm outside: |
| Depth | 18 mm outside: |
| Colour | Front face: white (RAL 9003) |

Environment

| | |
|---------------------------------------|---------------------------------------|
| Standards | IEC 60695-2-11 IEC 529 EN 50102 |
| Fire Resistance | Door: 650 °C Front face: 650 °C |
| Ik Degree Of Protection | IK07 |
| Ambient Air Temperature For Operation | -25...60 °C |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 3.100 cm |
| Package 1 Width | 29.400 cm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|------------|
| Package 1 Length | 50.200 cm |
| Package 1 Weight | 628.000 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 6 |
| Package 2 Height | 52.000 cm |
| Package 2 Width | 30.000 cm |
| Package 2 Length | 40.000 cm |
| Package 2 Weight | 6.288 kg |
| Unit Type Of Package 3 | P12 |
| Number Of Units In Package 3 | 96 |
| Package 3 Height | 120.000 cm |
| Package 3 Width | 80.000 cm |
| Package 3 Length | 120.000 cm |
| Package 3 Weight | 112.608 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Product

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |