

# Product data sheet

Specifications



Socket-outlet, Merten System M, 2P + E, 16A, Schuko, screwless terminals, glossy, polar white

MTN2311-0319

## Main

|                               |  |
|-------------------------------|--|
| Aesthetic Name                | M-Arc<br>System M<br>M-Plan glass<br>M-Elegance<br>M-Plan<br>M-Star<br>M-Smart |
| Device Presentation           | Mechanism with central plate   |
| Outlet Standard               | German   |
| Product Or Component Type     | Socket-outlet  |
| Socket Additional Information | Shuttered<br>With hinged lid   |

## Complementary

|                                |                        |
|--------------------------------|------------------------|
| Outlet Poles Configuration     | 2P + E                 |
| Wiring Device Mounting         | Flush                  |
| Fixing Mode                    | By screws and claws    |
| Colour Tint                    | Polar white (RAL 9010) |
| Connections - Terminals        | Screwless terminals    |
| Rated Current                  | 16 A                   |
| [Ue] Rated Operational Voltage | 250 V                  |

## Environment

|                         |      |
|-------------------------|------|
| Ip Degree Of Protection | IP20 |
|-------------------------|------|

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type Of Package 1       | PCE      |
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 4.600 cm |
| Package 1 Width              | 7.000 cm |
| Package 1 Length             | 7.000 cm |
| Package 1 Weight             | 84.000 g |
| Unit Type Of Package 2       | BB1      |
| Number Of Units In Package 2 | 10       |
| Package 2 Height             | 9.400 cm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                              |           |
|------------------------------|-----------|
| Package 2 Width              | 18.400 cm |
| Package 2 Length             | 27.000 cm |
| Package 2 Weight             | 952.000 g |
| Unit Type Of Package 3       | CAR       |
| Number Of Units In Package 3 | 60        |
| Package 3 Height             | 30.600 cm |
| Package 3 Width              | 34.100 cm |
| Package 3 Length             | 40.500 cm |
| Package 3 Weight             | 6.144 kg  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Compliant<br><a href="#">EU RoHS Declaration</a>  |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope)                 |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Weee                     | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile      | No need of specific recycling operations  |