

Product data sheet

Specifications



Socket-outlet, Merten System Design, 2P + E, 16A, Schuko, hinged lid, shutter, screwless terminals, IP44, lotus white

MTN2314-6035

Main

Range	Merten
Product name	System Design
Product or component type	Socket-outlet
Device presentation	Mechanism with fixing frame and central plate

Complementary

Device mounting	Flush
Fixing mode	By screws and claws
Device application	Power supply
Socket number	1
Outlet poles configuration	2P + E
Outlet standard deviation	Schuko
Outlet standard	CEE 7/3
Cover type	Hinged lid With shutter
Rated current	16 A
[Ue] rated operational voltage	250 V
Network type	AC
Network frequency	50/60 Hz
Colour tint	Lotus white
Material	Thermoplastic
Surface finish	Matt
Connections - terminals	Screwless terminals
IP degree of protection	IP44
Width	71 mm
Height	71 mm
Depth	45 mm
Standards	DIN 49440

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.3 cm
Package 1 Width	7.6 cm
Package 1 Length	7.6 cm
Package 1 Weight	115.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	50
Package 2 Height	19.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	6.155 kg

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

Recommended replacement(s)