

Product data sheet

Specifications



Cover frame, Merten D-Life, 3 gangs, mocca

MTN4030-6552

Main

Range	Merten
Aesthetic Name	D-Life
Product Or Component Type	Cover frame

Complementary

Number Of Gangs	3 gangs
Colour Tint	Mocca
Surface Finish	Metallic
Surface Treatment	Varnished
Material	Zamak
Ip Degree Of Protection	IP20
Height	90 mm
Width	234 mm
Depth	12 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.200 cm
Package 1 Width	9.900 cm
Package 1 Length	24.500 cm
Package 1 Weight	198.000 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	58
Package 2 Height	30.500 cm
Package 2 Width	33.900 cm
Package 2 Length	40.700 cm
Package 2 Weight	12.010 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Well-being performance

 Rohs Exemption Information [Yes](#)

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
--------------------------	---

China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
------------------------------	---

Environmental Disclosure	Product Environmental Profile
---------------------------------	---

Circularity Profile	No need of specific recycling operations
----------------------------	--