

Product data sheet

Specifications



Thermostat, Merten, Room, 24 V, System design, anthracite

MTN5761-6034

⚠ Discontinued on: Apr 15, 2024

⚠ Discontinued

Main

Range	Merten
Product Or Component Type	Thermostat
Product Name	System Design
Device Presentation	Mechanism with fixing frame and cover plate
Device Application	Room

Complementary

Device Mounting	Flush
Technology Type	Electromechanical
Function Available	With thermal feedback With bimetal sensor With temperature reduction
[Ue] Rated Operational Voltage	24 V
Fixing Mode	By screws
[In] Rated Current	10 A
Hysteresis	0.5 K
Contacts Type And Composition	1 NO
Number Of Terminals	8 screwless terminals
Colour Tint	Anthracite (RAL 7024)
Material	ABS (acrylonitrile butadiene-styrene): central plate
Surface Treatment	Varnished
Height	71 mm
Width	71 mm
Depth	47 mm

Environment

Measurement Temperature	5...30 °C
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	6.0 cm
Package 1 Width	7.5 cm
Package 1 Length	7.5 cm
Package 1 Weight	89.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	40
Package 2 Height	18.5 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.96 kg