


Product data sheet

Specifications



U.motion KNX Server Plus, Touch 15

MTN6260-0415

 **Discontinued on:** Sep 30, 2021

 **Discontinued**

Main

Range Of Product	U.motion
Range Compatibility	KNX
Product Or Component Type	Server + touch panel
Device Short Name	Touch 15
Product Destination	KNX bus system U.motion system
Product Compatibility	U.motion touch panel Client Touch 7 smartphone tablet PC
Bus Type	Ethernet KNX
Operating System	Linux
Display Size	15.6 inch
Display Colour	65000 colours
Colour Tint	Aluminium

Complementary

Connector Type	1 RJ45 4 USB
Integrated Connection Type	Loudspeaker Microphone
Device Mounting	Flush
[Ue] Rated Operational Voltage	100...240 V AC
Maximum Power Consumption In W	25 W operation
Control Type	Touch screen
Display Type	TFT
Display Resolution	1366 x 768 pixels WXGA
Illuminating Intensity	300 cd
Function Available	Visualisation
Memory Type	1 GB DDR2 SDRAM
Mounting Position	Horizontal
Material	Plastic and metal
Height	525 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	306 mm
Depth	92 mm
Net Weight	6 kg

Environment

Ambient Air Temperature For Operation	0...30 °C
Ip Degree Of Protection	IP20 conforming to EN 60529

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	28 cm
Package 1 Width	47 cm
Package 1 Length	69.5 cm
Package 1 Weight	7.775 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Eu Rohs Directive [Compliant](#)
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)
Pro-active China RoHS declaration (out of China RoHS legal scope)