

# Product data sheet

Specifications



## KNX ARGUS Presence 180/2.20 m flush-mounted, nickel metallic, System Design

MTN6302-6050

### Main

Range	KNX
Aesthetic Name	System Design D-Life
Product Or Component Type	Presence detector
Bus Type	KNX
Colour Tint	Nickel

### Complementary

Device Presentation	Mechanism with central plate
Number Of Channels	5
Protection Type	Creep zone protection
Type Of Setting	Light sensitivity adjustable
Duty Cycle	15300 minutes
Time Delay Range	0...1 s (switch-on)
Detection Face	Lateral: 8 m
Detection Angle	180° horizontal
Material	Polycarbonate
Surface Treatment	Varnished
Device Mounting	Flush
Mounting Height	2.2 m

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.9 cm
Package 1 Width	7.5 cm
Package 1 Length	7.5 cm
Package 1 Weight	99.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	30
Package 2 Height	18.5 cm
Package 2 Width	30.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Length	40.0 cm
Package 2 Weight	3.38 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		<a href="#">REACH Declaration</a>
Eu Rohs Directive		Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation		<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee		The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins