

# Product data sheet

Specifications



## KNX ARGUS Presence 180/2.20 m flush-mounted, champagne metallic, System Design

MTN6302-6051

### Main

Range	KNX
Aesthetic Name	D-Life System Design
Product Or Component Type	Presence detector
Bus Type	KNX
Colour Tint	Champagne

### Complementary

Device Presentation	Mechanism with central plate
Number Of Channels	5
Protection Type	Creep zone protection
Type Of Setting	Light sensitivity adjustable
Duty Cycle	15300 minutes
Time Delay Range	0...1 s (switch-on)
Detection Face	Lateral: 8 m
Detection Angle	180° horizontal
Material	Polycarbonate
Surface Treatment	Varnished
Device Mounting	Flush
Mounting Height	2.2 m

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.9 cm
Package 1 Width	7.5 cm
Package 1 Length	7.5 cm
Package 1 Weight	99.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	30
Package 2 Height	18.5 cm
Package 2 Width	30.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Length	40.0 cm
Package 2 Weight	3.38 kg

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation