

Product data sheet

Specifications

U.motion - KNX Server



MTN6501-0001

⚠ Discontinued on: Sep 30, 2021

⚠ Discontinued

Main

Range Of Product	U.motion
Range Compatibility	KNX
Product Or Component Type	KNX server
Product Compatibility	U.motion touch panel Client Touch 7 smartphone tablet PC
Bus Type	KNX Ethernet
Provided Equipment	Plug-in screw terminals USB stick with additional software and documentation

Complementary

Connector Type	1 RJ45
Mounting Support	TH35 DIN rail conforming to EN 60715
[Ue] Rated Operational Voltage	12...24 V DC
Power Consumption In W	3 W 240 mA at 12 V
18 Mm Pitches	9
Height	95 mm
Width	162 mm
Depth	63 mm

Environment

Ip Degree Of Protection	IP20
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7 cm
Package 1 Width	11 cm
Package 1 Length	20.6 cm
Package 1 Weight	420 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information