

# Product data sheet

Specifications



Switch, Mureva Styl, complete product, 1-pole 2-way, electromechanical, 10AX, LED, IP55, grey

MUR35024

## Main

Range Of Product	Mureva Styl
Device Presentation	Complete product
Technology Type	Electromechanical
Number Of Rocker	1
Colour Tint	Grey (RAL 7016)

## Complementary

Device Mounting	Surface
Switch Function	1-pole 2-way
Actuator	Rocker
Rated Current	10 AX
Load Type	Load for energy saving lamps with ballast: 100 W
[Ue] Rated Operational Voltage	250 V AC
Local Signalling	LED (blue)
Led Current Consumption	0.15 mA at 250 V
Condition Of Use	Indoor/outdoor
Material	SEBS ABS (acrylonitrile butadiene-styrene) Brass
Fixing Mode	By screws
Clamping Connection Capacity	1.5...2.5 mm² for rigid cable(s) 1.5...2.5 mm² for stranded cable(s) 1.5...2.5 mm² for flexible cable(s)
Wire Stripping Length	13 mm
Cable Entry	Easy valve access diameter: 6...20 mm
Chemical And Detergent Products Resistance	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane
Height	76 mm
Width	76 mm
Depth	64 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Projecting Depth	64 mm
------------------	-------

## Environment

Quality Labels	AENOR EAC CE NF
Ip Degree Of Protection	IP55
Ik Degree Of Protection	IK08
Flame Retardance	Self-extinguishing 650 °C conforming to IEC 60695-2-1
Standards	EN 60669-1
Ambient Air Temperature For Operation	-5...40 °C
Ambient Air Temperature For Storage	-25...55 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.600 cm
Package 1 Width	6.500 cm
Package 1 Length	7.600 cm
Package 1 Weight	124.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.000 cm
Package 2 Width	17.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	1.330 kg
Unit Type Of Package 3	S04
Number Of Units In Package 3	60
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	8.807 kg

# Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging   Transparency   RoHS/REACH

## Resource performance

Sustainable Packaging

## Well-being performance

Mercury Free

Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations