

Product data sheet

Specifications



Switch, Mureva Styl, mechanism, 1-pole 2-way, electromechanical, 10AX, LED, IP55, white

MUR39024

Main

Range Of Product	Mureva Styl
Device Presentation	Mechanism
Technology Type	Electromechanical
Number Of Rocker	1
Colour Tint	White (RAL 9003)

Complementary

Device Mounting	Surface Flush
Switch Function	1-pole 2-way
Actuator	Rocker
Rated Current	10 AX
Load Type	Load for energy saving lamps with ballast: 100 W
[Ue] Rated Operational Voltage	250 V AC
Local Signalling	LED (blue)
Led Current Consumption	0.15 mA at 250 V
Condition Of Use	Indoor/outdoor
Material	ABS (acrylonitrile butadiene-styrene) SEBS Brass
Fixing Mode	By screws
Clamping Connection Capacity	1.5...2.5 mm² for rigid cable(s) 1.5...2.5 mm² for stranded cable(s) 1.5...2.5 mm² for flexible cable(s)
Wire Stripping Length	13 mm
Chemical And Detergent Products Resistance	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane
Height	71 mm
Width	71 mm
Depth	40 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Quality Labels	AENOR NF EAC CE
Ip Degree Of Protection	IP55
Ik Degree Of Protection	IK08
Flame Retardance	Self-extinguishing 650 °C conforming to IEC 60695-2-1
Standards	EN 60669-1
Ambient Air Temperature For Operation	-5...40 °C
Ambient Air Temperature For Storage	-25...55 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	7.1 cm
Package 1 Length	7.1 cm
Package 1 Weight	55 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	8 cm
Package 2 Width	16.2 cm
Package 2 Length	39.5 cm
Package 2 Weight	644 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	60
Package 3 Height	30 cm
Package 3 Width	40 cm
Package 3 Length	60 cm
Package 3 Weight	4.704 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging Transparency RoHS/REACH

Resource performance

✔ Sustainable Packaging

Well-being performance

✔ Mercury Free

✔ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations