

Product data sheet

Specifications



Genesis - 1 SO - Italian - 1 module - 10A 250VAC - white

MWD130317516

Main

Product or component type	Socket-outlet
Socket number	1
Outlet standard	Italian
Outlet poles configuration	2P + E
Device presentation	Complete product
Colour tint	White

Complementary

Device mounting	Flush
Number of modules	1 module
Rated current	10 A at 250 V AC 50/60 Hz
Fixing mode	Clip-in
Material	PC (polycarbonate)
Surface finish	Glossy
Connections - terminals	Screw clamp terminal
AWG gauge	AWG 12
Embedding depth	25 mm
Projecting depth	8 mm
Width	115 mm
Height	75 mm
Depth	33 mm

Packing Units

Package 1 Weight	2040.000 g
Package 1 Height	19.000 mm
Package 1 width	14.000 mm
Package 1 Length	56.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile