

# Product data sheet

Specifications



## Genesis - 2 SO - American 2P + E15 A 250 V - white

MWD130317544

### Main

Range	Genesis
Product or component type	Socket-outlet
Outlet standard	American
Outlet poles configuration	2P + E
Device presentation	Complete device
Type of packing	Flow-pack

### Complementary

Device mounting	Flush
Number of modules	3 modules
Rated current	15 A at 250 V AC 50/60 Hz
Colour tint	Socket-outlet: white Cover frame: white
Fixing mode	By screw
Material	PC (polycarbonate): socket-outlet ABS (acrylonitrile butadiene-styrene): cover frame
Surface finish	Socket-outlet:glossy Cover frame:glossy
Connections - terminals	Screw terminals
AWG gauge	AWG 12
Embedding depth	16.0 mm
Projecting depth	9.0 mm
Width	75.0 mm
Height	113.0 mm
Depth	25.0 mm
Net weight	0.061 kg

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	66.0 g

Package 1 Height	1.9 cm
Package 1 width	1.4 cm
Package 1 Length	2.8 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>