

Product data sheet

Specifications

Genesis - 1 SO - Euroamerican - 2P - 16/15A 250VAC - white



MWD60120

Main

Range	Genesis
Product or component type	1 socket-outlet
Outlet standard	Euroamerican
Outlet poles configuration	2P
Device presentation	Complete product
Provided equipment	Screws
Type of packing	Flow-pack

Complementary

Device mounting	Flush
Rated current	15/16 A at 250 V AC
Fixing mode	Screw
Material	ABS (acrylonitrile butadiene-styrene)
Connections - terminals	Screw clamp terminal
AWG gauge	AWG 12
Embedding depth	31 mm
Projecting depth	8 mm
Width	114 mm
Height	75 mm
Depth	39 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	36.0 g
Package 1 Height	7.6 cm
Package 1 width	3.2 cm
Package 1 Length	11.9 cm
Unit Type of Package 2	BB1

Number of Units in Package 2	40
Package 2 Weight	1584.0 g
Package 2 Height	19 cm
Package 2 width	14 cm
Package 2 Length	56 cm

Offer Sustainability

EU RoHS Directive	Under investigation
--------------------------	---------------------
