

# Product data sheet

Specifications



## Genesis - 2 SO - American 2P + E15 A 250 V - beige

MWD61601

### Main

Range	Genesis
Product or component type	Socket-outlet
Outlet standard	American
Outlet poles configuration	2P + E
Device presentation	Complete device
Type of packing	Flow-pack

### Complementary

Device mounting	Flush
Number of modules	3 modules
Rated current	15 A at 250 V AC 50/60 Hz
Colour tint	Socket-outlet: beige Cover frame: beige
Fixing mode	By screw
Material	PC (polycarbonate): socket-outlet ABS (acrylonitrile butadiene-styrene): cover frame : cover frame
Surface finish	Socket-outlet:glossy Cover frame:glossy
Connections - terminals	Screw terminals
AWG gauge	AWG 12
Embedding depth	16.0 mm
Projecting depth	9.0 mm
Width	75.0 mm
Height	113.0 mm
Depth	25.0 mm
Net weight	0.061 kg

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.064 kg

<b>Package 1 Height</b>	7.6 cm
<b>Package 1 width</b>	2.5 cm
<b>Package 1 Length</b>	11.7 cm

## Offer Sustainability

<b>Sustainable offer status</b>	Green Premium product
<b>REACH Regulation</b>	<a href="#">REACH Declaration</a>
<b>REACH free of SVHC</b>	Yes
<b>EU RoHS Directive</b>	Compliant <a href="#">EU RoHS Declaration</a>
<b>Toxic heavy metal free</b>	Yes
<b>Mercury free</b>	Yes
<b>RoHS exemption information</b>	<a href="#">Yes</a>
<b>China RoHS Regulation</b>	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
<b>Environmental Disclosure</b>	<a href="#">Product Environmental Profile</a>