

Product data sheet

Specifications



ClimaSys Exchanger air-water 3150W techo

NSYCEW2100W230VR

ⓘ Discontinued

Main

Range	ClimaSys
Product Name	ClimaSys CE
Product Or Component Type	Air-water exchanger
Mounting Type	On top of enclosure
Cooling Power	2100 W

Complementary

Pressure	1 MPa for water
Flow Rate	External circuit: 250 m3/h
Control Type	Thermostat
Temperature Setting Range	25...50 °C
Controlled Fluid	Water
Input Voltage	230 V 50/60 Hz
[In] Rated Current	0.5 A
Inrush Current	1 A
Power Consumption In W	90 W
Output Type	Inverter contact
Height	310 mm external:
Width	600 mm external:
Depth	365 mm external:
Net Weight	26 kg
Noise Level	64 dB
Material	Steel
Colour	Grey (RAL 7035)
Condition Of Use	The enclosure must be at least IP54 Outside temperature could be higher than inside temperature

Environment

Ip Degree Of Protection	IP54 conforming to DIN 40050
Product Certifications	UL

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------