

Product data sheet

Specifications



Cable gland SNAP-IN quick fixing M20, polyamide IP68 UL approved UV resistant

NSYCGSP20

Main

Range	Spacial
Product Or Component Type	Cable gland
Accessory / Separate Part Category	Cable management accessory
Range Compatibility	Spacial Spacial CRN Spacial Spacial S3D Spacial Spacial S3X
Mounting Location	Enclosure top Enclosure bottom
Cable Entry	Cable gland M20
Device Composition	1 cable gland 1 seal
Quantity Per Set	Set of 20
Material	Seal: CR (chloroprene) Body: PA (polyamide) 6

Complementary

Colour	Grey (RAL 7035)
Fixing Mode	Push and turn clockwise
Net Weight	0.015 kg

Environment

Product Certifications	UL VDE
Environmental Characteristic	UV resistant
Flame Retardance	V2 conforming to UL 94
Ambient Air Temperature For Operation	-20...100 °C permanent -30...150 °C intermittent
Ip Degree Of Protection	IP68 conforming to IEC 60529 5 bar, 30 min

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	3.0 cm
Package 1 Length	4.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	15.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	20
Package 2 Height	2.5 cm
Package 2 Width	17.0 cm
Package 2 Length	22.0 cm
Package 2 Weight	318.0 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	40
Package 3 Height	11.0 cm
Package 3 Width	19.0 cm
Package 3 Length	19.0 cm
Package 3 Weight	750.0 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)