

# Product data sheet

Specifications



Signalling beacon adapter, square  
50 mm RAL 7040. For S3CM HMI  
encl.

NSYCMACS50

## Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Adaptor for signalling beacon
Device Application	Multi-purpose
Enclosure Nominal Dimensions	-
Mounting Location	On fixed brackets
Mounting Support	Signalling beacon Option of passing cables through the inside For 50 mm square tube
Range Compatibility	Spacial Spacial S3CM
Device Composition	1 adaptor 1 nut
Quantity Per Set	Set of 1

## Complementary

Material	Adaptor: aluminium
Colour	Adaptor: grey (RAL 7040)
Surface Finish	Epoxy-polyester powder
Fixing Mode	Direct fixing - on fixed brackets of enclosure location
Permanent Permissible Load	0.025 kg
Height	0 mm
Diameter	14 mm
Net Weight	0.11 kg

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	15.2 cm
Package 1 Length	15.5 cm
Package 1 Weight	110.0 g
Unit Type Of Package 2	PAL
Number Of Units In Package 2	10

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Height	20.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	600.0 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations